




1	2	3	4	5
---	---	---	---	---



TECHNICAL CHARACTERISTICS

MATERIAL
INSULATOR MATERIAL: PBT
FLAMMABILITY RATING UL94-V0
COLOUR: BLACK
CONTACT MATERIAL: COPPER ALLOY
CONTACT TYPE: STAMPED
CONTACT PLATING: SELECTIVE GOLD
SHIELDING: BRONZE NI PLATED
QUALITY CLASS: 500 MATING CYCLES


ENVIRONMENTAL
OPERATING TEMPERATURE: -40 °C UP TO 85 °C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
CURRENT RATING: 1.5 A
WORKING VOLTAGE: 120 VAC
INSULATION RESISTANCE: >500 mOHM
DIELECTRIC WITHSTANDING VOLTAGE: 1 000 VAC/MN
CONTACT RESISTANCE: 20 mOHM MAX

STANDARD
 CERTIFIED: E324776

SOLDERING
WAVE PROCESS ONLY

PACKAGING
TRAY

RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = $\pm$ 0.2 .XX = $\pm$ 0.15	 DESCRIPTION: HORIZONTAL SHIELDED DUAL PORT 8P8C MODULAR JACK TAB DOWN WERI PART NO: 615016137621		SIZE A4
G								
F								
E	03-JAN-14	UL & TEMP UPDATE	QL					
D	28-AUG-13	DIM UPDATE	QL	APPROVAL: RJ	UNIT: MM			
C	12-NOV-12	DIM	GG		SCALE:			
B	06-OCT-09	UL STANDARD	JP		SHEET: 1/1			
A	21-NOV-07	PDF	CH		DRAW:			
REV	DATE	FILE	BY					