


**STRADA-C-GD LENSES FOR OSRAM-OS
DRAGON SERIES OF LEDs**

- Specially designed for Osram-os Golden Dragon Plus LEDs.
- New extremely wide BATWING design with very and uniform light distribution.
- Lens material optical grade PMMA. Allows use of high current and temperature conditions
- Best available optical efficiency, approximately 95%.
- Fastening to heat sink with or without PU foam adhesive tape of automotive grade, please select which suits the best for your needs.



LENS TYPES

NAME	ORDERING CODE	FWHM Angle
Strada-CGD	C10915_Strada-C-GD	$\pm 73^\circ$
Strada-C-GD-TAPE	C10916_Strada-C-GD-tape	$\pm 73^\circ$

EULUMDAT & IES FILES AVAILABLE BY REQUEST


MEASUREMENT DATA

Relative Intensity of C10915_Strada-C-GD




© Ledil Oy – PRELIMINARY - Subject to change without prior notice

DRAWING





Isometric view

Bottom view




Front view



Isometric view

Top view



Material: PMMA

Part no. lens only:
C10915 (height: -0.15mm)

This drawing is our property.
It can't be reproduced
or communicated without
our written agreement.



Ledil Oy
Tehdaskatu 13
FIN-24100 SALO
Finland

DRAWING TITLE

Datasheet Strada-C-GD Assy

DRAWN BY
ol

DATE
16.12.2009

CHECKED BY
hh

DATE
16.12.2009

SIZE
A4

DRAWING NUMBER
CA10916

REV
1

DESIGNED BY
ol

DATE
16.12.2009

SCALE 2:1 WEIGHT(g)

SHEET 1/1

© Ledil Oy – PRELIMINARY - Subject to change without prior notice