

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [19084-0008](#)
Status: **Active**
Overview: [Solderless Terminals](#)
Description: Open Barrel Star Ring , Tin-Plated Steel, for 14-18 AWG Wire Range, Stud Size 8 (M4)

Documents:
[Drawing \(PDF\)](#) [Product Specification PS-19902-011 \(PDF\)](#)
[Product Specification PS-19902-006 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
UL E32244

General

Product Family Ring and Spade Terminals
Series [19084](#)
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview [Solderless Terminals](#)
Product Name N/A
Type Ring
UPC 800755080223

Physical


Barrel Type Open
Insulation None
Material - Plating Mating Tin
Net Weight 0.758/g
Packaging Type Reel
Plating min - Mating 2.540µm
Plating min - Termination 2.540µm
Stud Size 8 (M4)
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter N/A
Wire Size AWG 14, 16, 18
Wire Size mm² 0.80 - 2.00

Material Info

Old Part Number SRZ-S-4129-08

Reference - Drawing Numbers

Product Specification PS-19902-006, PS-19902-011
Sales Drawing SD-19084-001



Series

image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[19084Series](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
ASP Perishable	0190290053
Tool Kit used in ASP presses that process metal strip product	
Mini-Mac™	0638815600
Applicator	