

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [19044-0138](#)
Status: **Active**
Overview: [High-Temperature Temp Terms Terminals and Splices](#)
Description: Krimptite™ Ring Tongue Terminal for 14-16 Heavy Duty AWG Wire

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#)

Agency Certification

CSA LR18689
UL E32244

General

Product Family Ring and Spade Terminals
Series [19044](#)
Comments Heavy Duty
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview [High-Temperature Temp Terms Terminals and Splices](#)
Product Name Krimptite™
Type Ring
UPC 800753050822

Physical


Barrel Type Closed
Insulation None
Material - Plating Mating Tin
Net Weight 3.189/g
Packaging Type Adhesive Tape on Reel
Plating min - Mating 2.540µm
Plating min - Termination 2.540µm
Stud Size 1/2" (M12)
Termination Interface: Style Crimp or Compression
Wire Size AWG 14, 16
Wire Size mm² 1.30 - 2.00

Material Info

Old Part Number B-101-12HDT

Reference - Drawing Numbers

Product Specification PS-19902-011
Sales Drawing SD-19044-008



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[19044Series](#)

Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
Perishable Tooling	0190270135
Spacers for tape product	
ATP Perishable	0190270301
Tool Kit used in ATP	
Presses that Process	
Product on Tape	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

19044-0138