


Wamco Part No.	Envelope Size	Base Type	Rating	Filament Shape
WL-43	T-3¼	BA9s	2.5V .500A	C-2R

Test Volts	Current (A)			Light Output (MSCP)			Life Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
2.5	.450	.500	.550	.375	.500	.625	3,000 Hrs

Dimensional Characteristics:

1. L.C.L. = .78" (19.8 mm)
2. Base = Nickel-plated Brass Construction.
3. ANSI Standard No. 43
4. Part Mark: WL-43



			Title:	
			T-3¼ Miniature Bayonet Base Lamp	
			2.5V .500A Vacuum	
Revised	01/24/12	EB	Notes: Unless otherwise specified, all dimensions are in mm.	Rev: 2
Drawn	06/08/09	SL		
Checked	06/08/09	EB		
Approved	06/09/09	EB		