


ROHS-COMPLIANT

LTR	REV.	DESCRIPTION	DATE
△*2	B	ECR # 111206-2 ADD LENGTH	12/06/11'



NOTE:

- 1.CABLE: NON-UL 28AWG(7/0.127 T.C)*25C+DRAIN WIRE(26AWG 7/0.16)
+AL-FOIL/MYLAR PVC JACKET;
OD: $\phi 7.0 \pm 0.2$ mm, COLOR: BEIGE(NK-A03).
- 2.CONNECTOR:
P1&P2: DB25P MALE GOLD FLASH CONTACT,NICKEL PLATED SHELL.
- 3.HOOD: MOLDED TYPE, PVC 45P, COLOR: BEIGE(NK-A03)
- 4.ELECTRICAL TEST : 100% OPEN SHORT MIS WIRE TEST .
CONTACT RESISTANCE 3Ω MAX .
INSULATION RESISTANCE $10M\Omega$ MIN .
- 5.PACKING: EACH PC / Maxxtro ZIPBAG(L) + LABEL

P1	1	2	3	4.....23	24	25	SHELL
							DRAIN
P1	1	2	3	4.....23	24	25	SHELL

DWG	P/N	L±T(mm)	BAR CODE	LABEL
120-3295-4	100237	6000±50		LABEL 4
120-3295-3	100210	1000±20		LABEL 3
120-3295-2	100231	3000±30	7612320111996	LABEL 2
120-3295-1	100211	1800±30	7612320111989	LABEL 1

Tolerance Inch M/M			Maxxtro®			
.X	.015	.30	Title DB25/M - DB25/M CABLE			
.XX	.010	.10				
.XXX	.005	.05				
Draw FANNIE 12/06/11'			Customer P/N			
Chk [Signature]			App'd [Signature] Customer: T-JPC			
Engr [Signature]			Scale	NONE	Units	m/m
			Dwg No.	120-3295	REV:B	Sheet 1/2