

PART
NAME

NEMA 4X ENCLOSURE

PART
No.

AN-1316, AN-1316-G, AN-2816 & AN-2816-B

REV.
DATE


2-12-04

MATERIAL: ALUMINUM ALLOY #ADC-10


FINISH: NATURAL (NO SUFFIX)

GRAY (SUFFIX -G)



SMOOTH BLACK (SUFFIX -B)

FOUR (4) M4 x 25mm (0.975") LG. SCREWS
SUPPLIED FOR ASSEMBLY.TWO (2) M3.5 x 6mm LG. NICKEL PLATED
SCREWS AND WASHERS SUPPLIED FOR
GROUNDINGALL DIMENSIONS HAVE ± 0.015 TOLERANCE
UNLESS OTHERWISE SPECIFIED0.136 DIA. x 0.310 DEEP
(6) HOLES
ACCEPTS EITHER M3.5 METRIC
OR #6 STD. SHEET METAL
SCREWS x 0.250 LG.
(NOT SUPPLIED)




SECTION "B-B"

* DIMENSIONS ARE AT
BOTTOM OF ENCLOSURE


DETAIL "D"



SECTION "A-A"



BODY



COVER

SECTION "C-C"

PART NO. AN-2816 & AN-2816-B
ARE SUPPLIED WITH A WELDED
ON MOUNTING BRACKET ONLY.