

Technical datasheet: FT-27T-4.0B1-471

Specifications:

Resonant Frequency	4.0kHz $\pm$ 0.5kHz
Max Resistance (Zr)	500 Ω
Capacitance	20000nF $\pm$ 30%nF

Dimensions:

Type B: (D: Ø27mm, d: Ø20mm, T: 0.42mm, t: 0.20mm)

