


8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC.. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	4/5/10	D.GRIFFIN
B	ECN 4906: CLARIFY PIN 1 AND ADD DIELECTRIC CALL OUT	7/14/10	D/FRISIELLO
C	ECN 5671: CN RELEASE	8/22/11	D.FRISIELLO
D	ECN 5868: ADDED LENGTHS 03 M, 075 M	12/8/11	D.FRISIELLO



MODEL NUMBER	LENGTH METERS [FEET]
CAU3AA-03M	0.3 [.98]
CAU3AA-05M	0.5 [1.64]
CAU3AA-075M	0.75 [2.46]
CAU3AA-1M	1.0 [3.28]
CAU3AA-2M	2.0 [6.56]
CAU3AA-3M	3.0 [9.84]
CAU3AA-5M	5.0 [16.41]

NOTES:

CABLE: UL STYLE 20276, 2X, TWISTED PAIR, 30AWG WITH ALUM/POLY FOIL SHIELD AND DRAIN WIRE. ONE UNSHIELDED TWISTED PAIR, 30AWG. 2 COND., 24AWG. OVERALL BRAID SHIELD, 65% JACKET: PVC, BLUE (PANTONE 300C)

MISCELLANEOUS:
CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.
CABLE ASSEMBLY MUST MEET USB 3.0 REQUIREMENTS.
CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005 PROJECTION 	APPROVALS DRAWN BY D.FRISIELLO CHECKED BY M.MARTINEZ APPROVED BY S.SMITH	DATE 4/1/10 4/1/10 4/1/10	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY USB 3.0	
	COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION CA, USB 3.0 TYPE A-M TO TYPE A-M	
	SIZE A	FSCM NO. 43321	DWG. NO. CAU3AA	REV. D
SCALE: NONE CAD FILE: CAU3AA.SLDDRW SHEET 1 OF 1				