

<b>TECHNICAL SHEET</b>	Brand name <b>SAFE ! LUX</b>	
Référence <b>45411</b>	Description <b>SAFELUX 38W</b>	N° : <b>FT45411</b> Page(s) : <b>1/1</b>

## Technical information


In : nominal power	-
Un : nominal voltage	AC 230V
f in Hz : frequency	50 Hz
T° color	Daylight
IRC	85
Cable Type :	HO7RNF 2x1mm <sup>2</sup>
Luminous Flux (Lumen) :	2300
IP : protection	IP 65
IK : shock	IK 10
Life time (Hours) :	8000 heures (5 to 6 years)
Weight : in Kg	2,7 Kg
Dim : (Lxlxh) en mm	345 x 280 x 140 mm
Color :	RAL Blue Reflex
Unit per box :	1
Protection class :	Class II
Custom code :	94054035
Gencod :	3700300600104
IEC Certifications :	EN60598-1 & EN60598-2-4

Picture :



Functions:

Used on base, on tripod, hang on the wall or on metallic surface.



Description :

The professional worklight SAFE! LUX 38 with its 2D fluo compact low consumption lamp, does not burn and does not heat. It is the ideal Lighting to avoid all accidents due to direct manipulation, after several hours of use. Connected to the correct alimentation source, the SAFE! LUX offers an homogenous light similar to day light which does not dazzle and is the warranty of an optimum visibility.

Use :

The SAFE! LUX 38 is the best professional lighting. Shock resistant, it is the best solution for all applications when a polyvalent and safe lighting is required.

Created : 03/06/04

Modified :

Indice :

By : G.BRACCINI