

THIS DRAWING IS UNPUBLISHED.




RELEASED FOR PUBLICATION

,19 .

© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	P	F	REVISIONS						
				ZONE	LTR	DESCRIPTION			DATE	APPD
GP	00				L	REVISED PER EC 0513-0300-04			24SEP04	JG



SECTION A-A

- 1 HOUSING FULLY LOADED WITH CONTACTS.
- 2 NUMBER ON CONTACT INDICATES WIRE RANGE.
- 3 CONTACT INSULATION RANGE: .060 MAXIMUM O.D.
- 4 CONTACTS PLATED GOLD PLATED FOR LENGTH OF .150 MIN FROM MATING END, .000030 MIN GOLD IN MATED AREA. .000100-.000200 BRIGHT TIN OR BRIGHT IN TIN-LEAD AREA SHOWN. .000050 NICKEL UNDERPLATE ON ENTIRE CONTACT.
- 5 CONTACTS PLATED GOLD PLATED FOR LENGTH OF .150 MIN FROM MATING END, GOLD FLASH IN MATED AREA. .000100-.000200 BRIGHT TIN OR BRIGHT IN TIN-LEAD AREA SHOWN. .000030 NICKEL UNDERPLATE ON ENTIRE CONTACT.
- 6 CONTACTS PLATED GOLD PLATED FOR LENGTH OF .150 MIN FROM MATING END, .000030 MIN GOLD IN MATED AREA. .000100-.000200 MATTE TIN IN AREA SHOWN. .000050 NICKEL UNDERPLATE ON ENTIRE CONTACT.

	6	2	#22-26	745207-7
OBSOLETE	5	3	#20-22	745207-6
OBSOLETE	5	2	#22-26	745207-5
OBSOLETE	4	1	#26-30	745207-4
OBSOLETE	4	3	#20-22	745207-3
OBSOLETE	4	2	#22-26	745207-2
OBSOLETE	4	1	#26-30	745207-1
	FINISH	2	AWG WIRE RANGE	PART NUMBER

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± .005 ANGLES ± 2°		DR 4-6-90 J GALLUCCI BG		AMP AMP INCORPORATED Harrisburg, Pa. 17105		
MATERIAL HOUSING: BLACK THERMOPLASTIC 94V-0 RATED CONTACTS:PHOSPHOR BRONZE		CHK 6-21-90 W.LENKER				
FINISH SEE TABLE		APPD 6-22-90 J.WESTMAN		NAME PLUG ASSEMBLY, SIZE 2, 15 POSITION, AMPLIMITE™		
		APPD 6-22-90 J.ASSINI				
		PRODUCT SPEC 108-40011				
		APPLICATION SPEC 114-40002		SIZE C	FSCM NO 00779	DRAWING NO 745207
		WEIGHT -		SCALE 4:1		SHEET 1 OF 1