

Order symbol: AR14127CHSS
Product nbr: 8561045
Description: PC Enclosure
Remarks: Hinged opaque cover w/S.S.
Quick release latch

EAN: 6418074067050
El. number:
Finland:
:
Norway:

Including: Hinged cover base with 10-32 brass inserts, latched cover with formed in place PUR gasket, and stainless hinge pin. Quick release latches. (Latch options available.)
Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:		Length	Width	Height	Rating:
mm:		356	305	178	Ingress Protection (EN 60529): 66/67
inch:		14.0	12.0	7.0	Electrical insulation: Totally insulated
Materials:					Halogen free (DIN/VDE 0472, Part 815): yes
Material:		Polycarbonate			UV resistance: UL 508
Base colour:		RAL 7035 -light grey			Flammability Rating (UL 746 C 5): complies with UL 508
Cover colour:		RAL 7035			Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws material:		Stainless steel			NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13
Gasket material:		Polyurethane			Certificates:
Temperatures:					Underwriters Laboratories
Short term:		-40 ... 140 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 284 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
ABP1412		Painted Steel Back Panel			
ALBP1412		Aluminum Back Panel			
ADFP1412		Dead Front Panel w/ screws			
ASP1412		Aluminum Swing Panel			
ASPK1412		Swing Panel Kit incl. Panel			
ASPHK14		Swing Panel Kit w/o Panel			
AMFL12		12" Mounting Flange Set			

