





CIRCUIT: SPDT CONTACT CONFIGURATION		
POS 1	POS 2	POS 3
↙	↗	→
OFF	DN	DN

LEGEND
○ = OFF POSITION
■ = INDICATES KEY PULL
X = INDICATES NO KEY PULL



- NOTES:
1. ALL DIMENSIONS IN MM [INCH]
 2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
 3. TERM. NOS. FDR REFERENCE ONLY.
 4. RATING: 2A @125VAC, 1A @250VAC
 5. CONTACT RESISTANCE: 10mILLI-OHMS max.
 6. DIELECTRIC STRENGTH: 1000 VAC-1Minute
 7. INSULATION RESISTANCE: 200Mega OHMS min.
 8. MATERIALS:

HOUSING: ZINC ALLOY DIE CAST, SATINE CHROME PLATING
CYLINDER: ZINC ALLOY W/SATIN CHROME PLATING
TERMINAL AND CONTACTS: SILVER PLATED
KEYS (2) KEY CODE 10001:
TUBULAR STEEL, NICKLE PLATING

REV.	ECN No.	DESCRIPTION	DATE	CHKD
A	11737	RELEASED FOR PRODUCTION	10/12/01	CJB

TITLE				
K0124D-10001				
SCALE	DATE	DR	DWG	REV
1.5:1	10/12/01	CJB	K500106	A

E-SWITCH®