

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0908611001](#)
Status: **Obsolete**
Overview: [rast_25_connector_system](#)
Description: 2.50mm (.098") Pitch Appli-Mate RAST 2.5 Header, Right Angle, 5 Circuits

Documents:
[Drawing \(PDF\)](#)

General

Product Family	PCB Headers
Series	90861
Application	Signal, Wire-to-Board
Overview	rast_25_connector_system
Product Name	RAST 2.5

Physical

Breakaway	No
Circuits (Loaded)	5
Circuits (maximum)	5
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Plating Mating	Tin
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.81mm (.150")
PCB Retention	None
Packaging Type	Bag
Pitch - Mating Interface	2.50mm (.098")
Pitch - Termination Interface	2.50mm (.098")
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-20°C to +85°C
Termination Interface: Style	Through Hole


Electrical

Current - Maximum per Contact	2A
Voltage - Maximum	32V

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-90860-001
Product Specification	PS-99020-0040
Sales Drawing	SDA-90861



EU RoHS Not RoHS Compliant REACH SVHC Not Reviewed Low-Halogen Status Not Reviewed	China RoHS 
--	--

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[90861Series](#)

Mates With
[90871](#) Appli-Mate RAST 2.5 IDT Housing