


THIS DRAWING IS UNPUBLISHED.
 RELEASED FOR PUBLICATION
 - . - .
 © COPYRIGHT - BY TYCO ELECTRONICS CORPORATION.
 ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION		DATE	DWN	APVD
				D	E			
HM	00			REDWN & ADD: 6/1; NRP 97-053 & EC 0801-0009-97		24MAR97	GG	JK
				REV-ECO-08-022455		16SEP08	LH	SJ



1. ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY
UNLESS OTHERWISE SPECIFIED.

2. MATERIAL: COPPER IRON ALLOY, 0.46 [.018] THICK.

3. SPLICE CONNECTOR MARKED WITH "TE PART
NUMBER, UL LOGO, CSA LOGO AND 10/12 AWG"
ON FAR SIDE.

4. APPLICATION: UNDERCARPET POWER CABLING;
SEE INSTRUCTION SHEET 408-3128.

UNDERCARPET	553454-1		
APPLICATION	PART NO.		
Tyco Electronics	Tyco Electronics Corporation Harrisburg, PA 17105-3608		
NAME	CONNECTOR, SPLICE, 10/12 AWG		
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-553454	—
CUSTOMER DRAWING		SCALE 4:1	1 OF 1 REV E

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN G. GARRETT	24MAR97
CHK G. GARRETT	24MAR97
APVD J. KILPATRICK	24MAR97
PRODUCT SPEC	—
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC	± —
1 PLC	± —
2 PLC	± —
3 PLC	± —
4 PLC	± —
ANGLES	± —
MATERIAL △2	FINISH
WEIGHT	—
CUSTOMER DRAWING	