




Home> Products > Trimmers> 343 > Product Page

Order Product and Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- Test and Measurement Catalog
- RoHS Product List
- Customer Feedback

343P1MEG



Actual product appearance may vary.

343 Series Trimmer, 1 MOhm, 0.75 W, 20 Turns, Rectangular Body, Horizontal Shaft

Features

- 20-turns
- 0.75 Watt
- Cermet element
- Low cost
- Low profile - only 6.35 mm (1/4 in) high
- brush contact and unique "T" slider
- block design assure CRV of 3 % or 3
- Ohms contact idles at stops

Potential Applications

- Voltage divider circuits
- Telecommunications

Description

The 343 Series is a low profile, 19.05 mm (3/4 in.) rectangular, multturn trimmer. Made in accordance to MIL-R-22097 standards, the 343 is sealed for cleaning in common solvents.

Supporting Documentation

 [Dimensions](#)

Product Specifications	
Product Type	Trimmer
Watts	0.75 W
Turns	20
Element Type	Cermet
Resistance Value	1 MOhm
Resistance Tolerance	± 10 %
Temperature Coefficient	± 100 ppm/ °C
Body	19,05 mm [0.75 in] rectangular
Shaft Location	Horizontal
Rotational Life	200 cycles
Series Name	343
Availability	Global
UNSPSC Code	4111363300
UNSPSC Commodity	4111363300 Potentiometers

My Links

- Login to iCOM
- Login as Rep/AD
- Login as Guest
- Login to Digital University

Keyword Search

Search for product and support information.

All Sensing and Control

Product Search

Part number search:

Use (*) to expand search

Specification Search