

790-024P
Crimp Terminated Cable Receptacle Connector,
Pin Contacts
How To Order









Series 79
 Cable
 Connectors

790-024P Cable Receptacles
PIN CONTACTS WITH CRIMP TERMINATION



Rugged, lightweight 790-024P connectors feature machined aluminum shells, fluorosilicone face seals and wire grommets for environmental protection. Contacts are rear-release snap-in crimp type. Connectors are supplied with crimp contacts packaged separately. Size #23 signal pins accept up to #22 AWG wire. Size #16 contacts accept #16-18 AWG wire. Size #12 contacts accept #12-14 AWG wire. Size 12 and 16 cavities also accept coaxial contacts purchased separately. Connector shell features a groove for attachment of a low-profile EMI backshell adapter 799-015, ordered separately.

HOW TO ORDER				
Sample Part Number				
790-024P	C-13	M	P	
Base Part Number	Shell Size - Insert Arrangements	Shell Finish	Hardware Option	
790-024P Cable Receptacle with Pin Contacts	<p>See Table 1 for Available Insert Arrangements.</p> <p>To order a connector without size #16 or #12 power pins, substitute "W" instead of "P" in the insert arrangement.</p> <p>Example:</p> <p>36P2 is supplied with 2 power pins.</p> <p>36W2 is supplied less the power pins.</p> <p>See Section B for coaxial contacts purchased separately.</p>	<p>M Electroless Nickel general purpose applications</p> <p>MT Nickel-PTFE 1000 Hour Grey™ maximum corrosion protection and durability (non-reflective grey)</p> <p>ZNU Zinc-Nickel with Black Chromate tactical applications (non-reflective black)</p> <p>Additional shell finishes are listed on page C-9.</p>	 N Thru-Hole No Hardware  L Low-Profile Captivated Jackscrew, Hex Head  S Low-Profile Captivated Screwlock, Hex Head	 P Female Jackpost  K Slot-Head Extended Jackscrew  T Slot-Head Extended Captivated Screwlock

SPECIFICATIONS

Current Rating	#23 5 AMPS, #16 13 A., #12 23 A.
Dielectric Withstanding Voltage	#23 500 VAC RMS, #12 and #16 1800 VAC RMS
Insulation Resistance	5000 megohms minimum
Operating Temperature	-65° C. to +150° C.
Shock	300 g.
Vibration	37 g.

MATERIALS AND FINISHES

Shell	Aluminum alloy
Contacts	Copper alloy, 50 microinches gold plated
Insulators	Liquid crystal polymer (LCP)
Retention Clips	Beryllium copper alloy
Interfacial Seal, Grommet	Fluorosilicone rubber
Hardware	300 series stainless steel

Dimensions in Inches (millimeters) are subject to change without notice.

790-024P
Crimp Terminated Cable Receptacle Connector,
Pin Contacts
How To Order

Table I Contact Arrangements

Layout	Contact Quantity	#23 #16 #12	Face View
A-5	5		
B-2P2	2		
B-9	9		
C-13	13		
D-15	15		
D-3P3	3		
D-7P2	5 2		
E-11P2	9 2		
E-19	19		
E-7P3	4 3		
F-15P2	13 2		
F-23	23		
F-5P5	5		
G-33	33		
H-10P4	6	4	
H-29P7	22 7		
H-36P2	34	2	
H-54P2	52 2		
H-5P5		5	
H-66	66		
J-17P4	13 4		
J-25P2	23 2		
J-33	33		
J-7P7	7		
K-27P4	23 4		
K-35P2	33 2		
K-43	43		
K-9P9	9		
L-6P6		6	
L-78	78		
M-102	102		

CROSS-SECTIONAL VIEW OF 790-024P









TABLE 2 HARDWARE OPTION

	N No Mating Hardware Connector is supplied with thru-holes. Shell sizes H and L are .148" (3.76) diameter, other shell sizes are .092" (2.34) diameter. Accepts standard Micro-D M83513 hardware.		P Jackposts Connector is supplied with removable jackposts. Shell sizes H and L have #4-40 UNC thread, other sizes have #2-56 thread. Stainless steel. Conforms to M83513/05.
	L Hex Head Jackscrews Connector is supplied with stainless steel non-removable low profile jackscrews. Shell sizes H and L have #4-40 UNC thread, other sizes have #2-56 thread.		K Extended Jackscrews Connector is supplied with stainless steel slot head non-removable jackscrews. Shell sizes H and L have #4-40 UNC thread, other sizes have #2-56 thread.
	S Hex Head Screwlocks Connector is supplied with stainless steel non-removable low profile screwlocks. Shell sizes H and L have #4-40 UNC thread, other sizes have #2-56 thread. Screwlocks allow the connector to be mated before the screws are fastened.		T Extended Screwlocks Connector is supplied with stainless steel slot head screwlocks. Shell sizes H and L have #4-40 UNC thread, other sizes have #2-56 thread. Screwlocks allow the connector to be mated before the screws are fastened.

Dimensions in Inches (millimeters) are subject to change without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Glenair](#):

[790-024PD-3P3EK](#)