


3.0X1.0mm(1104) RIGHT ANGLE BI-COLOR SMD CHIP LED



UNIT : MM[INCH]

TOLERANCE : $\pm 0.2[\pm 0.0079]$ UNLESS OTHERWISE NOTED

Selection Guide

Part No.	Dice	Lens Type	Iv (mcd) @20mA		Viewing Angle
			Min.	Typ.	2θ 1/2
APBA3010SRSYWPR	SUPER BRIGHT RED (GaAlAs)	WHITE DIFFUSED	40	70	140°
	SUPER BRIGHT YELLOW(InGaAlP)		50	100	

APPROVED:

J. Lu

CHECKED:

J. Chao

DRAWN :

L.N. Sheu

SCALE :

10 : 1

DATA NO. : F9354

V.1

DATE : OCT/26/2000