


LOC	DIST	REVISIONS					
DF	S0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			C	REV PER ECO-05-002595	07-05	AA	DE

1. MARKED PER MIL-STD-130.
- 2

TOLERANCE OF LEAD LENGTH:
UP TO 24 INCHES [609.6] = $\pm .12$ [± 3.0]
24 INCHES [609.6] & UP = 1%
3. OPERATING VOLTAGE: 50 KVDC AT 0 TO 70,000 FEET,
-55°C TO 125°C.
- 4

PIGTAIL IS SOLDER DIPPED.
5. TO MATE WITH WITH AMP LGH-4
RECEPTACLE WITH 2.00 [50.80] BARREL DEPTH.
- 6

INSULATION CUT, BUT NOT REMOVED.



6	74.00 [1879.6]	5-445058-2
6	39.00 [990.6]	5-445058-1
4	74.00 [1879.6]	445058-2
4	39.00 [990.6]	445058-1
REMARKS	A DIM	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	18-DEC-89	tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608		
		CHK	18-DEC-89			
DIMENSIONS: INCHES [mm]		D.EABY	18-DEC-89	NAME		
		D.EABY	18-DEC-89			
		APVD	18-DEC-89	LEAD ASSY SGL END LGH-4		
		D.EABY	18-DEC-89			
MATERIAL SEE CALLOUTS		PRODUCT SPEC		SIZE		
		APPLICATION SPEC				
		FINISH		CAGE CODE		
		WEIGHT	-	DRAWING NO		
		CUSTOMER DRAWING		SCALE		
				SHEET		
				OF		
				REV		