



Similar to image

Technical data:		
Number of NC contacts		1
Number of NO contacts		3
Mounting depth	mm	64
Number of pitch units for width		2
Switching capacity real power / for filament lamp load	W	1,500
Type of voltage		AC/DC
• for operating		AC
• of the operating voltage		AC
Control supply voltage / rated value	V	230
Operating current / rated value	A	24
Operating voltage / rated value		
• minimum	V	440
• maximum	V	440
Protection class IP		IP20
Product extension / can be installed / supplementary device		Yes
Product component / slide for manual operation		No

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Global Industry Mall (Online ordering system)

<http://www.siemens.com/lowvoltage/mall>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


<http://support.automation.siemens.com/WW/view/en/5TT5731-0/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TT5731-0

Tender specifications

[Datanorm](#) [GAEB81](#) [GAEB83](#) [RTF](#) [TXT](#)



¹⁾ Dimension without sealable terminal cover.



last change:

Nov 22, 2010