




REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
01 ₀	RELEASED	6/3/98	6/3/1998

DESIGNED FOR USE WITH 0.085 SR CABLE	
CABLE ENTRY DIAMETER MINIMUM	
HOUSING	.089
CONTACT	.0204

HOUSING	STAINLESS STEEL PER ASTM-A484 AND ASTM- A582, TYPE 303	GOLD PLATE PER MIL-G-45204
DIELECTRIC	PTFE FLUOROCARBON PER ASTM-D-1457	N/A
CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204
EMI GASKET	CONDUCTIVE ELASTOMER PER MIL-G-83528	N/A
COMPONENT	MATERIAL	FINISH

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES		DRAWN BY <i>[Signature]</i> DATE 9/4/97		M/A-COM a Division of AMP Incorporated	
FRAC. DEC. ANGLES ± 1/64 ± .005 ± 1°		CHECKED BY <i>[Signature]</i>		140 Fourth Avenue	
		APPD BY <i>[Signature]</i> 6/3/1998		Waltham, MA 02154-7577	
These drawings and speci- fications are the property of M/A COM Interconnect Div. and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale o f item(s) without written permission.		USE ASSY PROCEDURE 408-04880 NO. A.P. (90-025)		TITLE FIELD REPLACEABLE 2-HOLE FLANGE MOUNT JACK RECEPTACLE DIRECT SOLDER ATTACHMENT	
		SIZE B	CODE IDENT NO. 26805	9024-5014-00	REV 01 ₀
		SCALE 5:1		SHEET 1 OF 1	

NOTES:
1. CAPTURED CENTER CONTACT

.XXX = in
XX.X = mm (REF)