




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		A3	REVISED PER ECO-11-004820	11MAR2011	RK	HMR
			A4	REVISED PER ECR-11-014651	20JUL2011	RK	DD
			A5	REVISED PER ECR-11-016987	5SEP2011	RS	DD


0.25 MAX
CUT-OFF

DIM E REF

- 1 BRASS, 0.20 THK. REF
- 2 NICKEL UNDERPLATE OVER ALL
- 3 0.00254 MIN THK BRIGHT TIN ENTIRE CONTACT OVER NICKEL UNDERPLATE
- 4 0.00038 THK GOLD STRIPE
- 5 TE CONNECTIVITY LOGO LOCATED APPROXIMATELY AS SHOWN
- 6 0.000762 THK GOLD STRIPE




SECTION T-T
SCALE 20:1



SECTION Y-Y
SCALE 20:1

18.24	2.40	2.60 2.20	1.55	1.96 1.57	1.30 - 1.60	22-24 AWG	ON REEL	6	3-2106124-3
18.24	2.40	2.60 2.20	1.55	1.96 1.57	1.30 - 1.60	22-24 AWG	LOOSE PIECE	2 3	2-2106124-7
18.24	2.40	2.60 2.20	1.55	1.96 1.57	1.30 - 1.60	22-24 AWG	ON REEL	2 3 4	2-2106124-3
18.24	2.40	2.60 2.20	1.55	1.96 1.57	1.30 - 1.60	22-24 AWG	ON REEL	2 3	2-2106124-2
18.24	3.01	2.80 2.40	2.05	2.32 1.92	1.70 - 2.10	18-20 AWG	LOOSE PIECE	2 3	2106124-9
18.24	3.01	2.80 2.40	2.05	2.32 1.92	1.70 - 2.10	18-20 AWG	ON REEL	2 3 4	2106124-3
18.24	3.01	2.80 2.40	2.05	2.32 1.92	1.70 - 2.10	18-20 AWG	ON REEL	2 3	2106124-2
DIM E	DIM D	DIM C	DIM B	DIM A	INSULATION DIA	WIRE RANGE	REMARKS	FINISH	PART NO



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±0.13
3 PLC ±
4 PLC ±
ANGLES ±1°
FINISH

SEE NOTES

DWN
R. BROWN
CHK
A. BUCHER
APVD
-

05MAR2009
05MAR2009
-

PRODUCT SPEC
108-2391
APPLICATION SPEC
114-13261
WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
CONTACT, TAB, CRIMP SNAP-IN
SLIM SEAL SSL
-

SIZE
A2

CAGE CODE
00779

DRAWING NO
2106124

RESTRICTED TO
-

SCALE
10:1

SHEET
1

OF
1

REV
A5