

NTE1819 Integrated Circuit Module, AF Power Amplifier, 30W/Ch

Features:

- Built-in muting circuit to cut off various kinds of pop noise
- Greatly reduced heat sink due to case temperature +125°C guaranteed

Absolute Maximum Ratings: ($T_A = +25^\circ\text{C}$ unless otherwise specified)

Maximum Supply Voltage, $V_{CC\text{max}}$	±42V
Thermal Resistance, Junction-to-Case, Θ_{j-c}	2.1°C/W
Junction Temperature, T_J	+150°C
Operating Case Temperature, T_C	+125°C
Storage Temperature range, T_{stg}	-30° to +125°C
Available Time for Load Shorted ($V_{CC} = \pm 27.5\text{V}$, $R_L = 8\Omega$, $f = 50\text{Hz}$, $P_O = 30\text{W}$), t_s	2sec

Recommended Operating Conditions: ($T_A = +25^\circ\text{C}$ unless otherwise specified)

Recommended Operating Voltage, V_{CC}	±27.5V
Load Resistance, R_L	8Ω

Operating Characteristics: ($T_A = +25^\circ\text{C}$, $V_{CC} = \pm 27.5\text{V}$, $R_L = 8\Omega$, $R_g = 600\Omega$, $V_G = 40\text{dB}$, R_L : non-inductive load, unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Quiescent Current	I_{CCO}	$V_{CC} = \pm 33\text{V}$	20	40	100	mA
Output Power	$P_{O(1)}$	THD = 0.4%, $f = 20\text{Hz}$ to 20kHz	30	—	—	W
	$P_{O(2)}$	$V_{CC} = \pm 25\text{V}$, THD = 1%, $R_L = 4\Omega$, $f = 1\text{kHz}$	35	—	—	W
Total Harmonic Distortion	THD	$P_O = 1\text{W}$, $F = 1\text{kHz}$	—	—	0.3	%
Frequency Response	f_L, f_H	$P_O = 1\text{W}$, +0dB/-3dB	20 to 50k			Hz
Input Resistance	r_i	$P_O = 1\text{W}$, $f = 1\text{kHz}$	—	55	—	kΩ
Output Noise Voltage	V_{NO}	$V_{CC} = \pm 33\text{V}$, $R_g = 10\text{k}\Omega$	—	—	1.2	mV _{rms}
Midpoint Voltage	V_N	$V_{CC} = \pm 33\text{V}$	-70	0	+70	mV
Muting Voltage	V_M		-2	-5	-10	V

Note 1. For power supply at the time of test, use a constant-voltage power supply unless otherwise specified.

Note 2. The output noise voltage is represented by the peak value on rms scale (VTVM) of average value indicating type. For AC power supply, use an AC stabilized power supply (50Hz) to eliminate the effect of flicker noise in AC primary line.

Pin Connection Diagram (Front View)

18	Input 2
17	NFB 2
16	GND
15	I Bias 2
14	Power GND 2
13	Output 2
12	Bootstrap
11	(+) V _{CC}
10	Output 1
9	Power GND 1
8	Mute t Cap
7	Mute Adjust
6	Muting
5	I Bias 1
4	Feedback
3	GND 1
2	NFB 2
1	Input 2

