

# TERMINAL BLOCKS

## PRINTED CIRCUIT

10A 2.5 <sup>□</sup> CEE REC 2  
GROUP 2

**A new range of printed circuit terminal blocks moulded in Noryl SE1 which provides for these terminals to be suitable for operating temperatures up to 120°C.**

Available with 1mm printed circuit pins at either 5mm pitch for up to 24 poles or 10mm pitch for up to 12 pole. Pressure plates are included in the terminal inserts as a standard whilst permanent marking against each individual pole for identification purposes is an optional extra.

Cat No.
15000
15001

To Order:

Please quote Cat. No. of required type and add number of poles required.  
e.g. Cat. No. 15000/16 = 16 pole 5mm pitch printed circuit terminal with pressure plates.


For permanent marking details and prices — please enquire.

### Cat. No. 15000

2 to 24 poles, standard screw terminals on top and p.c. pins at 5mm pitch. Including pressure plates.

### Cat. No. 15001

2 to 12 poles, standard screw terminals on top and p.c. pins at 10mm pitch. Including pressure plates.




# PCB TERMINALS & CONNECTORS


## 180° PCB Terminals - Noryl

**Housing:** Noryl SEI

**Colour:** Grey



Cat. Ref.	Pitch	Pack
15000	5.0	100
15001	10.0	100



Cat. Ref.	Applicable Standard	Wire Capacity	Rating	Volt.
15000	BS EN 60335 Part 1:1988	2.5 <sup>2</sup>	10A	250V
15001		2.5 <sup>2</sup>	10A	450V