


IEEE 1394 Firewire, 4 Pin Plug Solder Type 154-AVW10

KOBICONN

IEEE 1394 Firewire, 4 Pin Plug Solder Type



Dimensions: mm (In.)

Specifications	
Voltage:	30 VAC (R.M.S.)
Current:	1.0 Ampere max./ contact at 30°C T-Rise
Temperature:	80°C
Contact Resistance:	30 Miliohms max. initial
Insulation Resistance:	100 Megaohms min.
Dielectric Withstanding Voltage:	100 VAC at sea level
Contact Plating:	30μ" Au
Shell Plating:	Nickel plating
Clamp & SR Dimensions:	Clamp ø4.0mm, SR ø4.5mm

Date Last Revised: 12-20-04

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300177

154-AVW10

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[154-AVW10](#)