

► [Heatsinks f.cool](#)

► [Cases f.case](#)

▼ [Connectors f.con](#)

► [Sockets](#)

▼ [PCB connectors](#)

- [Male headers](#)
- [Female headers](#)
- [Direct female connector](#)
- [Jumpers](#)

► [IDC-connectors](#)

► [D-Sub connectors](#)

■ [Brackets for PC](#)


► [Optoelectronics](#)

Jumpers

CAB 5 05 G ...

for 0.6-0.64 mm wire wrap pins and Ø 0.6-0.7 mm The flexible contacts are shorting two pins. The jumpers can be mounted behind and next to each other.

[add to request](#) 



[Features](#)

[Technical Drawing](#)

[Variants](#)

no. of contacts	2
Oberfläche Kontakt / Kontakthülse	0,5µm Au 1µm Au 5µm Sn
surface of contact	0.5 µm gold
Einstecktiefe	4...5,5mm
Nennstrom	3 A
nominal voltage	250 V AC
Material Isolierkörper	PA 6
temperature range	-40 °C ... +105 °C
grid	5.08 mm
version	closed, hole for probe trip
colour	blue grey