

NICKEL METAL HYDRIDE SINGLE CELLS

PART NO.	X-REF/DESCRIPTION	VOLTS	mAh	DIAMETER x HEIGHT (MM)	(INCHES)
1/2AA-600NM	GP60AAH	1.2	600	14.5 x 30	.571 x 1.18
AA-1200NM	H-AA1200A CONSUMER TOP	1.2	1200	14.2 x 50	.559 x 1.97
AA-1400NM	H-AA1400A CONSUMER TOP	1.2	1400	14.2 x 50	.559 x 1.97
AA-1600NM	H-AA1600A CONSUMER TOP	1.2	1600	14.2 x 50	.559 x 1.97
AA-1650NM	HR-3U CONSUMER TOP	1.2	1650	14.2 x 50	.559 x 1.97
AA-1650NMFT	HR-AAU	1.2	1650	14.2 x 50	.559 x 1.97
AA-1700NM	H-AA1700A CONSUMER TOP	1.2	1700	14.2 x 50	.559 x 1.97
AA-1800NM	H-AA1800A CONSUMER TOP	1.2	1800	14.2 x 50	.559 x 1.97
AAA-600NM	H-AAA600A CONSUMER TOP	1.2	600	10.5 x 44.5	.414 x 1.75
AAA-650NM	HR-4U CONSUMER TOP	1.2	650	10.5 x 44.5	.414 x 1.75
AAA-720NMFT	HR-AAAU	1.2	720	10.5 x 44.5	.414 x 1.75
5/4AAA-700NM	H-5/4AAA-700A CONSUMER TOP	1.2	700	10.5 x 50	.414 x 1.96
5/4AAA-770NM	HR-5/4AAAU CONSUMER TOP	1.2	770	10.5 x 50	.414 x 1.96
2/3AF-1000NM	GP100AFH	1.2	1000	17 x 28	.670 x 1.10
4/5AF-2150NM	HR-4/5U	1.2	2150	17 x 43	.670 x 1.69
AF-2700NM	HR-AU	1.2	2700	17 x 50	.670 x 1.97
5/4AF-3800NM	HR-4/3AU	1.2	3800	17 x 67	.670 x 2.64
5/4AF-4000NM	HR-4/3FAU	1.2	4000	18 x 67	.670 x 2.64
5/4AF-4000NM-17	HR-4/3AU	1.2	4000	17 x 67	.670 x 2.64
5/4AF-4500NM	HR-4/3FAU	1.2	4500	18 x 67	.670 x 2.64
SC-2200NMH	HR-SC	1.2	2200	23 x 43	.906 x 1.69
SC-2500NMH	H-SC2500P	1.2	2500	23 x 43	.906 x 1.69
SC-3000NM	HR-SCU	1.2	3000	23 x 43	.906 x 1.69
C-3000NM	H-C3000A CONSUMER TOP	1.2	3000	26 x 50	1.02 x 1.97
C-4000NM	H-C4000A CONSUMER TOP	1.2	4000	26 x 50	1.02 x 1.97
D-7000NM	H-D7000A CONSUMER TOP	1.2	7000	34 x 61	1.34 x 2.40
D-7500NM	HR-D	1.2	7500	34 x 61	1.34 x 2.40
D-9000NM	H-D9000A CONSUMER TOP	1.2	9000	34 x 61	1.34 x 2.40

NI-CAD/NICKEL METAL HYDRIDE BUTTON CELLS



PART NO.	CHEMISTRY	X-REF/DESCRIPTION	VOLTS	mAh	DIAMETER x HEIGHT (MM)	(INCHES)
15FSNM	NIMH	V15H-VARTA 55601-101-000	1.2	15	11.5 x 3.1	.453 x .122
30SS	NICAD	GP30BVK	1.2	30	11.6 x 5.4	.457 x .213
40FSNM	NIMH	V40H-VARTA 55604-101-000	1.2	40	11.5 x 5.35	.453 x .211
40SSNM	NIMH	GP40BVH	1.2	40	11.6 x 5.4	.457 x .213
60SS	NICAD	GP60BVK	1.2	60	15.5 x 6.2	.611 x .244
80FSNM	NIMH	V80H-VARTA 55608-101-000	1.2	80	15.5 x 6.0	.611 x .236
80SSNM	NIMH	GP80BVH	1.2	80	15.5 x 6.2	.611 x .244
150FSONM	NIMH	V150H-VARTA 55615-101-000	1.2	150	OVAL	OVAL
170SS	NICAD	GP170BVK	1.2	170	25.1 x 6.7	.989 x .264
200FSMH	NIMH	V200H-VARTA FLARED CELL	1.2	200	25.1 x 6.7	.989 x .264
250FSMH	NIMH	V250H-VARTA 55625-101-000	1.2	250	25.1 x 6.7	.989 x .264
250SSNMH	NIMH	GP250BVH	1.2	250	25.1 x 6.7	.989 x .264
280SS	NICAD	GP280BVK	1.2	280	25.1 x 8.4	.989 x .335
300FSMH	NIMH	CP300H-VARTA 55630-101-000	1.2	300	25.1 x 7.55	.989 x .295
320SSNM	NIMH	GP320BVH	1.2	320	25.1 x 8.4	.989 x .335