


SIFAM's pushbuttons are moulded in a matt-finish nylon to match the style and appearance of other SIFAM control knobs. They are available, as standard, in black 5, grey 6, red 7 and white 44.

Should you have a requirement for special colours or shaft configurations, not covered by our standard range, please contact the Sales Office.

### Special Printing

We are happy to offer our printing facility to those customers requiring special markings on our pushbutton products. Letters, numbers, symbols or logos may be printed to provide a high quality, durable, versatile and cost-effective added feature.

Please note that minimum order quantities apply to printed pushbuttons and other special requirements.



### Ordering procedure

Please remember to quote the appropriate part number and shaft size together with the moulding colour required. For printed pushbuttons, please note that standard print colours are black onto white and grey mouldings and white onto black and red mouldings. When ordering printed pushbuttons please state legend required (min. 200 pieces per legend) and printing orientation (see below), for rectangular and illuminated products.



Horizontal  
printing orientation



Vertical  
orientation

### Packaging

Pushbuttons will be packed in boxes.

### Rectangular



### Illuminated



### Round/Tapered



### Square



### Cylindrical



7 Jul '00 14:34 P.01/02

ROXBURGH ELECTRONICS Fax: 01724281650









PB 03/50/000  
(RECESSED TOP)

3.3

PB 03/51/000  
(RECESSED TOP)

2.8

Maximum 1 line 3 characters  
2 lines 2 characters per line

|                                                                                     | Part Number                      | Shaft Size mm | Printing                                                                                                                                                  |
|-------------------------------------------------------------------------------------|----------------------------------|---------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------|
|    | PB 01/50/000<br>(RECESSED TOP)   | 3.3           | Maximum 1 line 6 characters<br>2 lines 6 characters per line<br><br>   |
|                                                                                     | PB 01/51/000<br>(RECESSED TOP)   | 2.8           |                                                                                                                                                           |
|                                                                                     | PB 07/50/000<br>(FLAT TOP)       | 3.3           |                                                                                                                                                           |
|                                                                                     | PB 07/51/000<br>(FLAT TOP)       | 2.8           |                                                                                                                                                           |
|    | 4/001/PB 11/50/000<br>(FLAT TOP) | 3.3           | Maximum 1 line 4 characters<br>2 lines 4 characters per line<br><br>   |
|                                                                                     | 4/001/PB 11/51/000<br>(FLAT TOP) | 2.8           |                                                                                                                                                           |
|   | 4/001/PB 11/51/000<br>(FLAT TOP) | 2.8           | Maximum 1 line 4 characters<br>2 lines 4 characters per line<br><br> |
|                                                                                     | 4/001/PB 11/51/000<br>(FLAT TOP) | 2.8           |                                                                                                                                                           |
|  | PB 02/50/000<br>(RECESSED TOP)   | 3.3           | Maximum 1 line 2 characters<br><br><br>                              |
|                                                                                     | PB 02/51/000<br>(RECESSED TOP)   | 2.8           |                                                                                                                                                           |
|                                                                                     | PB 08/50/000<br>(FLAT TOP)       | 3.3           |                                                                                                                                                           |
|                                                                                     | PB 08/51/000<br>(FLAT TOP)       | 2.8           |                                                                                                                                                           |
|  | PB 03/50/000<br>(RECESSED TOP)   | 3.3           | Maximum 1 line 3 characters<br>2 lines 2 characters per line<br><br> |
|                                                                                     | PB 03/51/000<br>(RECESSED TOP)   | 2.8           |                                                                                                                                                           |
|                                                                                     | PB 09/50/000<br>(FLAT TOP)       | 3.3           |                                                                                                                                                           |
|                                                                                     | PB 09/51/000<br>(FLAT TOP)       | 2.8           |                                                                                                                                                           |
|  | PB 04/50/000<br>(RECESSED TOP)   | 3.3           | Maximum 1 line 2 characters<br><br><br>                              |
|                                                                                     | PB 04/51/000<br>(RECESSED TOP)   | 2.8           |                                                                                                                                                           |
|                                                                                     | PB 10/50/000<br>(FLAT TOP)       | 3.3           |                                                                                                                                                           |
|                                                                                     | PB 10/51/000<br>(FLAT TOP)       | 2.8           |                                                                                                                                                           |