



- Multi-Tone Sounder in combination with Xenon Flash
- Integrated mounting bracket
- Optical and audible signal can be triggered separately
- Choice of different 8 tones
- Adjustable sound output
- High protection rating IP 65

TECHNICAL SPECIFICATIONS:

Dimensions (Diameter x Height):	91 mm x 120 mm
Housing:	PC/ABS-Blend; PC grey
Dome:	PC, transparent
Connection:	Screwable connection with wire protection max. 1.5 mm ²
Cable entry:	Membrane cover up to Ø 9 mm
Flash energy:	1 Ws
Flash frequency:	1 Hz
Sound output:	max. 100 dB
Fixing:	Bracket mounting
Life duration:	4 x 10 ⁶ flashes

ORDER SPECIFICATIONS:

	24 V ≅
red	423 120 75
yellow	423 320 75

Available from September 2005

TONE TYPES AND FREQUENCIES:

Tone A Tone type

No.	
1	Horn tone (c. 200 Hz)
2	Continuous (c. 2.3 KHz)
3	1 Hz tone (c. 2.3 KHz)
4	20 Hz whistle tone (c. 2.3 KHz)
5	800-970 Hz rising @ 1 Hz
6	2400-2850 Hz rising @ 7 Hz
7	1200-500 Hz falling @ 1 Hz
8	Alternating tone

