


## Heavy-Duty Power Cord, 15A, 14AWG (IEC-320-C19 to NEMA 5-15P) 10-ft.

MODEL NUMBER: **P034-010**



### Highlights

- C19 to 5-15P Power Cable, 10 ft.
- 14 AWG x 3C
- RoHS Compliant

### Package Includes

- C19 to 5-15P Power Cable, 10 ft.

### Description

Use Tripp Lite's P034-010 in server applications that require a higher rated, heavier gauge cable. IEC-60320-C19 to NEMA 5-15P connectors, 3 x 14 AWG conductors, 15A/125V rating.

### Features

- Molded, Heavy-Duty Power Cable, 10 ft.
- IEC-60320-C19 to NEMA 5-15P
- 14 AWG x 3C, SJT, 15A, 125 Volt
- RoHS Compliant

## Specifications

OVERVIEW	
Intended Application	Powering Devices
Cable Type	POWER
Model Type	Power Cords
INPUT	
Cable Length (ft.)	10
Cable Length (m)	3.05
UPC ASSIGNMENT	
Unit Carton UPC#	037332140920

<b>PHYSICAL</b>	
Color	Black
Style	Power Cables
<b>CONNECTIONS</b>	
Connector A	IEC-320-C19
Connector B	NEMA 5-15P
Number of Connectors	2
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.