




Hot air tools for do-it-yourself



WELDY PIC



WELDY PRO




WELDY PLUS





WELDY PLUS

digital hot air tool




- 1 terminal display with memory function
- 2 function programmes
- 3 temperature and airflow adjustment
- 4 Stand-by for eco-drive


- 5 tool stand
- 6 ergonomical distribution of weights
- 7 non-slip handle
- 8 main switch

Function programmes / digital display


By operating the key on the menu, the required function program can be selected




manuel drive



shrinking




forming




welding



soldering



paint stripping



drying



Intelligent hot air tools for do-it-yourself

BASIC WELDY PIC

ELECTRONIC WELDY PRO

DIGITAL WELDY PLUS



Technical data

Voltage	230,
Power consumption	1600 W
Temperature range	350°C or 500°C
Airflow	350 or 500 l/min
Max. static pressure	1250 Pa
Weight	500 g
On/off switch	2-step switch
Temperature adjustment	2-step
Airflow adjustment	2-step
Heating element	protected


Technical data

Voltage	230,
Power consumption	1800 W
Temperature range	100°C to 550°C
Airflow	250 or 550 l/min
Max. static pressure	1300 Pa
Weight	570 g
On/off switch	2-step switch
Temperature adjustment	potentiometer, stepless temperature adjustment with scale
Airflow adjustment	2-step
Elektronics	flicker-conformity
Heating element	protected

Technical data

Voltage	230,
Power consumption	2000 W
Temperature range	80°C to 650°C
Airflow	200 to 550 l/min adjustable
Max. static pressure	1200 Pa
Weight	620 g
On/off switch	main switch
Temperature and airflow adjustment	terminal with menu control
Display	LCD-display
Electronics	temperature control independent of airflow and power supply, program with seven function, memory, stand-by for eco drive flicker conformity
Heating element	all ceramic, protected

Accessories










Accessories



Accessories





**Intelligent Weldy hot air tools
for all budgets**

ISO 9001

SEV, CCA zertifiziert

CE-Konform

EcoTool

LEISTER

Riedstrasse, CH-6060 Sarnen/Switzerland

Tel. +41-41-662 75 88 Fax +41-41-662 75 02

e-mail: ecotool@ecotool.com

www.weldytool.com