


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	LENGTH	WEIGHT
T70C**6	72.00 ±.13 (1829 ±3.0)	.9 LB/72 IN (409 G/1829 mm)
T70C**8	96.00 ±.13 (2438 ±3.0)	1.2 LB/96 IN (545 G/2438 mm)
T70C**10	120.00 ±.13 (3048 ±3.0)	1.5 LB/120 IN (682 G/3048 mm)
T70C**2 (SEE NOTE 5)	(2000 mm ±3.0)	.98 LB/78.7 IN (447 G/2000 mm)

△ G △ C

- NOTES:
- SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
 - △ E THE T70C IS USED WITH THE T70B, T702B, AND TG70B.
 - △ B DIMENSIONS IN PARENTHESIS ARE IN METRIC.
 - △ D USE TWO (2) FEET OF T70C (COVER) FOR EVERY ONE (1) FOOT OF T702B (BASE).
 - ONLY AVAILABLE OUTSIDE NORTH AMERICA.



CAD FILENAME/LAYERS D35541CA_DC_T70C_03A.PRT

PANDUIT				CORP. TINLEY PARK, ILLINOIS			
T70 RACEWAY COVER				(T70C**6, T70C**8, T70C**10, T70C**2) △ G			
CUSTOMER DRAWING				UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .010 (.3) (XX) ± .03 (.8) ANGLES ± MAT'L:			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .010 (.3) (XX) ± .03 (.8) ANGLES ±				SCALE NONE			
DRAWN BY JBA				DATE 09-19-96			
CHECKED BY CEF				PVC			
ECN				35541-27			
DESCRIPTION				DRAWING NO. 35541-27			
REV				SIZE A			