



## DC013

### Multi Chemistry Corded/Cordless Radio Charger

#### Selling Proposition

- Runs off mains and 7.2 Volt to 18 Volt Li-ION/NiCd/NIMH batteries
- Blow molded protective roll cage with 6 impact resistance points for maximum job site durability
- Charges DEWALT 7.2 Volt to 18 Volt Li-ION/NiCd/NIMH batteries
- High efficiency weather resistant speakers with bass ports and bass boost for maximum job site listening experience
- Dual pivoting 28 mm flexible antenna provides more durability and better reception
- Digital tuner with LCD display, built-in clock, 10 FM and 5 AM station memory presets

#### Standard Equipment

- No batteries included

#### Warranty Specifications

- 1 year free service contract
- 1 year full warranty
- 30 Day No Risk Satisfaction Guarantee

Specifications	
Voltage	7.2 -18 V
Battery	Li-ION/NiMH/NiCd
Radio Power Source	AC - DC
Radio Frequencies	AM- FM Stereo
Charging Time	30-70 min
Length	490 mm
Height	290 mm
Weight	6.7 kg