


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

*PANDUIT PART NUMBER	A IN (mm)	B IN (mm)	T IN (mm)	WEIGHT LBS (g) / 100 FT
T38P-0	.375 (9.5)	.437±.047 (11.1±1.2)	.030±.010 (0.8±0.3)	1.28 lbs. (581 g)
T50P-0	.500 (12.7)	.500±.047 (12.7±1.2)	.030±.010 (0.8±0.3)	1.86 lbs. (844 g)
T100P-0	1.000 (25.4)	1.125±.047 (28.6±1.2)	.030±.010 (0.8±0.3)	3.90 lbs. (1769 g)

Notes;

- * 1) See current price sheet for part number suffix designations, package size and part color.
- 2) For roll sizes larger than 10ft., splicing may occur.
- 3) Reverse Cut



DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

CAD FILENAME/LAYERS	
---------------------	--

10D009BA_DC/01A_POLYPROPYLENE_SPIRAL_WRAP

PANDUIT

CORP. TINLEY PARK, ILLINOIS

(WEATHER RESISTANT)
POLYPROPYLENE SPIRAL WRAP
(CUSTOMER DRAWING)

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

(.X) ±	----	(.XXX) ±	----
(.XX) ±	----	ANGLES ±	----

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY LEF	DATE 11/11/11
-----------------	------------------

MAT'L:

SCALE	NONE
-------	------

DATE	6/9/10
------	--------

POLYPROPYLENE

DRAWING NO.

10D009BA-DC

DWG
A
SIZE

I	5/24/11	LEF	VJS	A B	ADDED ADDED	"" NOTE 3	REVERSE CUT	10D009BA	I	RAMI		
R	6/09/10	LEF	JVL	INITIAL RELEASE				10D009BA	R	RAMI		
REV	DATE	BY	CHK	DESCRIPTION				ECN - R	CUST	SUP		