

full line

PH ELECTRODE

Model : PE-03, PE-11, PE-01

ISO-9001, CE, IEC1010

PE-06HD, PE-04HD, PE-03K7, PE-05T



PE-11



PE-03



PE-01



PE-06HD



PE-05T



PE-03K7



PE-6HD

Lutron

LUTRON ELECTRONIC

The Art of Measurement

full line

pH ELECTRODE

PH ELECTRODE Model : PE-03	* General purpose, laboratory and field usage. * 12.3 mm dia. x 160 mm. * Epoxy body, 1 - 13 pH.
PH ELECTRODE Model : PE-11	* General purpose, laboratory and field usage. * 10 mm dia. x 130 mm. * Epoxy body. * 1 - 13 pH. (0 - 14 pH typical)
PH ELECTRODE	* Professional, laboratory and field usage. * 9.5 mm dia. x 130 mm. * Epoxy body. * 0 - 14 pH.
SPEAR TIP PH ELECTRODE Model : PE-06HD PE-04HD	* The "Spear Tip pH electrode" is perfect for those pH measurements in applications where sample piercing is required. Meat, sausage and cheese are ideal applications. The electrode features a very durable glass measuring spear packaged in a rugged virtually unbreakable epoxy body. * Range : 0 to 14 pH (PE-04HD) * Range : 1 to 13 pH (PE-06HD)
pH ELECTRODE + Temp. PROBE (combination kit of pH electrode) Model : PE-03K7	* One kit combine of PH electrode PE-03 and Temp. probe TP-07 as a whole unit. * Easy operation for the pH measurement under the ATC (Automatic Temp. Compensation). * Available for PH-208, PH-207, PH-207HA, PH-221 YK-2005WA.
pH electrode build in Temp. thermister inside. Model : PE-05T	pH electrode build in Temp. thermister inside. * pH meter when make the temperature compensation, * the extra optional Temp. probe is not necessary. Available for PH-207, PH-208, PH-207HA, PH-221, YK-2005WA, General purpose, laboratory & field usage. 1 to 13 pH (typical 0 to 14 pH). pH Operation Temp. : 5 to 60 °C (41 to 140 °F). * Temp. Probe Range : 0 to 60 °C (32 to 140 °F). * Epoxy Body Material. * Connector : * BNC plug for pH, ear phone plug for Temp.

* Appearance and specifications listed in this brochure are subject to change without notice. 0609-PHELECTRODE