



Artikel-Nr.: 730399

Bez.: TNC-Einbaubuchse, Einlochmontage, 50 ?



Mounting Holes



Impedance	50Ω
Frequency range	0 to 4GHz
Voltage rating	500 volts peak
Dielectric withstanding voltage	1500 volts rms
VSWR	M30012 straight connectors: 1.3 max. 0-4GHz M30012 right angle: 1.35 max. 0-4GHz
Other (MIL-C-39012 Cable Connectors)	Contact resistance: center contact 1.5 milliohm outer contact 0.2 milliohm Insertion loss: 0.2db max at 3 GHz (insulation resistance: 500 megohms)

TNC JACK SOLDER BULKHEAD

6	Lug	Brass	Nickel
5	Nut	Zinc	Nickel
4	Lock Washer	SK5	Nickel
3	Insulator	Delrin	White
2	Contact	PH/Bronze	Gold
1	Body	Brass	Nickel
NO	Description	Material	Finish

Dimensions Are In Millimeters
Unless Otherwise Specified

Tolerances
0.5-6 = ± 0.2
6-30 = ± 0.4
30-120 = ± 0.6
120-315 = ± 1.0
315-1000 = ± 1.6
1000-2000 = ± 2.4

www.bkl-electronic.de

Technische Änderungen vorbehalten. Ausführungen können variieren. Sollten Sie ein Muster benötigen kontaktieren Sie uns bitte.

BKL-ELECTRONIC Kreimendahl GmbH • Märkenstück 14 • 58509 Lüdenscheid

Tel: +49 (0)2351-3621-0 • Fax: +49 (0)2351-3621-29 • info@bkl-electronic.de

