






LOC	DIST	P	F	REVISIONS			DATE	APPROVED
				ZONE	LTR	DESCRIPTION		
CE	16				L	REV PER 0A00-0237-95	6-9-95	RH/FR

1. DIMENSIONS IN [] ARE IN INCHES
2. CONNECTOR WITHOUT KEY IS TYPE S
3 HOUSINGS: PBT MOLDING COMPOUND
NUT: PBT MOLDING COMPOUND
FERRULE ASSY: STAINLESS STEEL AND CERAMIC
INNER CRIMP RING: BRASS
OUTER CRIMP RING: COPPER
STRAIN RELIEF: POLYPROPYLENE
DUST COVER: THERMOPLASTIC RUBBER
4. INSTRUCTION SHEET 9373
5 BULK PACKAGED, 200 PER PACKAGE.



DUST COVER NOT SHOWN



MINIMUM BEND RADIUS PROTECTION

- 6 BULK PACKAGED 50 PER PACKAGE.
ORDER STRAIN RELIEF SEPARATELY.
DUALAN STYLE: 501783-1
ZIPCORD STYLE: 502016-1

6	125µm	501780-4
5	125µm	501780-3
	140µm	501780-2
	125µm	501780-1
FIBER SIZE		PART NO

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN mm TOLERANCES ON : 2 PL DEC ± 0.13 [.005] 3 PL DEC ± - ANGLES ± -	DR 5-19-88 B.BRIGGS	AMP AMP INCORPORATED Harrisburg, Pa. 17105			
	CHK 5-19-88 J.ZEIDERS				
	APPD 5-20-88 L.BUDD	NAME CONNECTOR KIT, DUALAN CABLE, AMP FSD			
APPD 5-20-88 D.THOMPSON					
PRODUCT SPEC -					
APPLICATION SPEC -					
WEIGHT -					
MATERIAL 3					
FINISH -	SIZE C	FSCM NO 00779	DRAWING NO 501780		
		SCALE 1 : 1			SHEET 1 OF 1

METRIC

RESTRICTED RELEASE
DRAWING MAY CHANGE WITHOUT
CUSTOMER NOTIFICATION