



VPB-1-1/4-0-SP Product Details

 [Share](#)

 [Print](#)

 [Email](#)



VPB-1-1/4-0-SP

TE Internal Number: 5580614002

 [Active](#)

Heat Shrink Tubing

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Heat Shrinkable Tubing
- Product Name = VPB
- Product Source = U.K., U.S.
- Flexible
- Medium Wall Style

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)

 [Request Sample](#)

 [Find Similar Products](#)

 [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [THERMOFIT VITON POLYMER BLEND TUBING Fluoroelastomer...](#) (PDF, English)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Heat Shrinkable Tubing
- Material = Polymer Blend Fluoroelastomer
- Color = Black

Electrical Characteristics:

- Product Source = U.K., U.S.
- [Expanded ID, Min. \(mm \[in\]\)](#) = 31.80 [1.252]
- [Recovered ID, Max. \(mm \[in\]\)](#) = 15.90 [0.6259]
- Product Use = Cables, Harnesses

Body Features:

- Product Name = VPB
- Pliancy = Flexible
- [Wall Style](#) = Medium
- [Wall Type](#) = Single
- [Shrink Ratio](#) = 2:1
- Fluid Type = Aviation Fuel, Chemicals/Solvents, De-Icing Fluid, Diesel Fuel, Lubricating Oil, Unleaded Gasoline
- Resistant To = Abrasion, Fluids, Wrinkling
- Wall Thickness - Full Recovery (Nominal) (mm [in]) = 1.39 [0.055]

Housing Features:

- Material Systems = Yes
- [Material Systems Code](#) = 30
- Flammability Rating Type = Flame-Retardant

Industry Standards:

- Government/Industry Qualification = No
- UL Rating = None
- CSA Certified = No
- Approved Standards = SC-X-15111
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Environmental:

- Fluid Resistance = Splash Protection
- [Operating Temperature \(°C\)](#) = -55 - +150

Conditions for Usage:

- Full Recovery Temperature (°C) = 175
- Shrink Temperature, Min. (°C) = 100
- High Temperature Compatible = Yes

Operation/Application:

- Application = Cable Jacketing, Wire Bundling
- Emission Free = No

Packaging Features:

- Packaging Method = Spool

Other:

- Brand = Raychem

Corporate Information

[About TE](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

Quick Links

[Check Distributor Inventory](#)

[Cross Reference Products](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

