


161-5330-E

2.5mm Mono Jack w/ Switch



SPECIFICATIONS

SPECIFICATIONS	
Housing:	LCP Black UL94V-0
Terminals:	Phosphor bronze silver plated
Tip Terminal:	Cu alloy silver plated
Insertion/ Ext Force:	.3-3 Kgs
Dielectric Strength:	250 VAC for 1 min.
Insulation Resistance:	100 M ohm minimum
Contact Resistance:	50 m ohm maximum
Life Cycle:	5000 matings minimum
Operating Temperature:	-25°C to +85°C
Voltage Rating:	16.0 VDC
Current Rating:	0.3 A
RoHS Compliant	

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

161-5330-E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-5330-E](#)