



[Home](#) > [Products](#) > > [8532-31](#) > 8532AK-31LF

[Add to myIDT \[?\]](#)

You may also like...

8532AK-31LF

Category:

Generic Part: 8532-31

Market Group: NETCOM

Description: 2 LVPECL OUT BUFFER



Parameters

Package	VFQFP 16 (NBG16)
Speed	NA
Temperature	C
Voltage	3.3 V
Status	Active
Sample	Yes
Minimum Order Quantity	75
Factory Order Increment	75

Distributor Inventory

No Pricing information is available from our Distributors at this time.

Documents

No documents available for this part at this time.

Package

Description	VFQFP-N 4 X 4 X 1.0 MM-NO LEAD
Class	PLASTIC
Moisture Sensitivity Level (MSL)	3
Category	Green
Moisture Exposure Floor Life	168 hrs. @ <30°C/60%RH
Peak Reflow Temperature	260°C
Rebake Conditions	48 hrs.@125°C
Length	4.0
Mark	K
Width	4.0
Pitch	0.65
Thickness	1.0
Status	Active