



3M Defense

- Products
- Capabilities
- Contracts
- About 3M Defense

Contact Us

United States > Products & Services > Manufacturing and Industry > 3M Defense US > Products > Air > New Build > Vibration Reduction > 3M™ Vinyl Foam Tape 4516 Black, 3/4 in x 36 yd, 12 per case

3M™ Vinyl Foam Tape 4516 Black, 3/4 in x 36 yd, 12 per case

UPC# 00021200033087 3M Product Number 4516-3/4"x36yd 3M ID 70002459041

Print Share



3M™ Vinyl Foam Tape 4516 is a vinyl, conformable, single-coated, closed-cell foam tape. 1/16 in thick.

- UV and solvent resistance
- Offers a moisture and dust seal
- Conformable
- General industrial, appliances, electrical and transportation.
- Sealing and vibration absorption.

Need Help?

Questions? 1-866-556-5712

Contact Us

Network Access Message: The page

- Overview
- Support

Bonds and seals to a variety of surfaces.

Specifications

Adhesive Type	Acrylic
Backing Material	Foam
Carrier Material	Vinyl
Color	Black
Density	25 Pound Per Cubic Foot
Diameter	10.9 Inch
Double Sided Adhesive	No
Industry - Use	Air, Appliance, Construction, General Industrial, Ground, Sea, Soldier, Transportation
Length	36 Linear Yard
Length (metric)	32.91 Linear Metre
Liner Color	White
Liner Thickness	3 Milli-inch (mil)
Liner Type	Paper
Product Category	Single-Sided Tapes
Product Form	Roll
Shelf Life	18 Month
Sub Industry	Equipment/Weapon Performance, Joinery/Outfitting/Insulation Department, Operations, Survivability
Tape Type	Single Coated
Temperature Resistance - Initial	250 Degree Fahrenheit
Temperature Resistance - Long Term	150 Degree Fahrenheit
Thickness	62 Milli-inch (mil)
Thickness (metric)	1.5 Millimetre
Units per Case	12
Width	0.75 Inch
Width (metric)	19.05 Millimetre

People who viewed this item also viewed



3M™ Adhesive Transfer Tape 468MP Clear, 1 in x 60 yd 5.0 mil, 36 per case Bulk