

Solutions for Electronic Specialty Markets (ESM)

- Product Catalog for Electronic Specialty Markets
- 3M™ Electronic Specialty Markets New Product Releases

3M™ Abrasives

3M™ Adhesives, Cleaners & Compounds

3M™ Breadboards & Test Clips

3M™ Cable & Assemblies

3M™ Copper Interconnects

3M™ Fiber Optics

3M™ Fire Protection

3M™ Heat Shrink

3M™ Identification Systems

3M™ Occupational Health & Safety Products

3M™ Protective Bumpers

3M™ Reclosable Fasteners

3M™ Splicing, Terminating & Ducting

3M™ Static Control

3M™ Tapes

3M™ Terminals, Kits & Tools

3M™ Vacuums & Accessories

3M™ Warehousing & Packaging Supplies

3M™ Wire Connectors

Other Tools

- What's New
- Sales Contacts
- U.S. Distributors

Search This Product Catalog


By Keyword

Go

[Product Catalog for Electronic Specialty Markets](#) [3M™ Terminals, Kits & Tools](#) [Forks](#) [Scotchlok™ Locking Fork Terminals](#) - [Vinyl Insulated Brazed Seam](#)

3M™ Scotchlok™ Vinyl Insulated Brazed Seam Locking Fork Terminal MV10 -6FLK, Stud Size 6

 [Printer-friendly format](#)



[\[click to enlarge\]](#)

This terminal has a wire range of 12 - 10 AWG and a stud size of 6. It comes in case quantities of 500 per case.

GTIN(UPC/EAN) : 0 00 54007 13949 2
3M Id : 80 - 6101 - 3423 - 3


Additional Information

The spring - like tongue locks into place around the stud even when the mount screw is not tightened. Extra force is required to remove it from the stud.

Learn More . . .

- [Packaging Data](#)
- [Locking Forks - Vinyl Insulated Brazed Seam 12 - 10 AWG - Product Selection Guide \(PDF 23.7 K\)](#)
- [Scotchlok Terminals MV18 - 4FL thru MV10 - 14FL - Data Sheet \(PDF 19.6 K\)](#)
- [Terminal Stud Size Chart - Product Selection Guide \(PDF 5.2 K\)](#)

Please Note:
Adobe® Acrobat® Reader is required to view PDF documents.



Characteristics

Agency Approvals	UL and CSA
Barrel Style	Brazed
China RoHS - Below MCV	No
CSA File Number	LR22190
EPC Can View	Public
EU RoHS Compliant	No
Insulation Material	Vinyl
Stud Size	6 American Wire Gauge (AWG)
Terminal Style	Locking
Terminal Type	Fork
UL File Number	E23438
Wire Gauge Range	10 to 12 American Wire Gauge (AWG)