



Product: [1370P](#)



Serial Digital Coax, RG59 Type, 20 AWG Solid BC, Foil + 85% TC Braid, CMP

Product Description

Video Cable, RG-59 Type 20 AWG solid bare copper, foam FEP insulation, Bonded Duofoil®+85% tinned copper braid, CMP Flamarrest® jacket.

Technical Specifications

Product Overview

Suitable Applications:	Commercial Video
------------------------	------------------

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
20	Solid	BC - Bare Copper	0.032 in	1

Conductor Count:	1
------------------	---

Insulation

Material	Material Trade Name	Nominal Diameter
FEP - Fluorinated Ethylene Propylene (Foam)	Teflon®	0.133 in

Outer Shield

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Tri-Laminate (Alum+Poly+Alum)	Duobond® II	100%
Braid	2	Tinned Copper (TC)		85%

Outer Jacket

Material	Material Trade Name	Nominal Diameter
PVC - Polyvinyl Chloride	Flamarrest®	0.192 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR	Outer Conductor DCR
10.1 Ohm/1000ft	4.1 Ohm/1000ft	4.1 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
16.1 pF/ft

Inductance

Nominal Inductance
0.097 µH/ft

Impedance

Nominal Characteristic Impedance
75 Ohm

Return Loss

Frequency [MHz]	Minimum Return (RL)
5 - 3000 MHz	15 dB

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.29 dB/100ft
3.58 MHz	0.62 dB/100ft
5 MHz	0.7 dB/100ft
7 MHz	0.82 dB/100ft
10 MHz	1.05 dB/100ft
67.5 MHz	2.2 dB/100ft
71.5 MHz	2.25 dB/100ft
100 MHz	2.7 dB/100ft
135 MHz	3.2 dB/100ft
143 MHz	3.25 dB/100ft
180 MHz	3.65 dB/100ft
270 MHz	4.55 dB/100ft
360 MHz	5.25 dB/100ft
540 MHz	6.4 dB/100ft
720 MHz	7.3 dB/100ft
750 MHz	7.5 dB/100ft
1000 MHz	9.4 dB/100ft
1500 MHz	12.8 dB/100ft
2250 MHz	17.5 dB/100ft
3000 MHz	21.9 dB/100ft

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.21 ns/ft	84%

High Frequency

Min. RL (Return Loss) [dB]
15 dB

Voltage

UL Voltage Rating
300 V RMS

Electrical Characteristics Notes:	Return Loss: Fixed bridge and termination
-----------------------------------	---

Temperature Range

UL Temperature Rating:	75°C
Operating Temperature Range:	0°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	24 lbs/1000ft
Maximum Recommended Pulling Tension:	37 lbs
Minimum Minor Axis Bend Radius:	2 in

Standards

NEC/(UL) Compliance:	CMP
CEC/C(UL) Compliance:	CMP
RG Type:	59

Applicable Environmental and Other Programs

Environmental Space:	Indoor - Plenum
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	No

Flammability, LSOH, Toxicity Testing

UL Flammability:	NFPA 262
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Related Part Numbers

Non-Plenum Number:	1370R
--------------------	-------

Variants

Item #	Color	Put-Up Type	Length	UPC
1370P 010500	Black	Reel	500 ft	612825113317
1370P 0101000	Black	Reel	1,000 ft	612825113300
1370P 006500	Blue, Light	Reel	500 ft	612825113232
1370P 0061000	Blue, Light	Reel	1,000 ft	612825113225
1370P 001500	Brown	Reel	500 ft	612825113157
1370P 0011000	Brown	Reel	1,000 ft	612825113140
1370P 008500	Gray	Reel	500 ft	612825113270
1370P 0081000	Gray	Reel	1,000 ft	612825113263
1370P N3U500	Green, Mil	Reel	500 ft	612825113133
1370P N3U1000	Green, Mil	Reel	1,000 ft	612825113126
1370P 003500	Orange	Reel	500 ft	612825113195
1370P 0031000	Orange	Reel	1,000 ft	612825113188
1370P 002500	Red	Reel	500 ft	612825113171
1370P 0021000	Red	Reel	1,000 ft	612825113164
1370P 007500	Violet	Reel	500 ft	612825113256
1370P 0071000	Violet	Reel	1,000 ft	612825113249
1370P 009500	White	Reel	500 ft	612825113294
1370P 0091000	White	Reel	1,000 ft	612825113287
1370P 004500	Yellow	Reel	500 ft	612825113218
1370P 0041000	Yellow	Reel	1,000 ft	612825113201

History

Update and Revision:	Revision Number: 0.331 Revision Date: 02-03-2025
----------------------	--

© 2025 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.