

Part Number

FMN.3M.330.XLCT

Size/Series 3MN / M

[Request a quote](#)

MECHANICAL DETAILS

Shell Style/Model	FM*: Straight plug with knurled grip and mold stop
Keying	
Housing Material	Environment friendly aluminium (nickel plated, anthracite color) shell and nut, other pieces bronze/brass
Cable Fixing	J : 0 - 0 mm
Variant	:


	A	B	C	D	F	L	M	P	X
mm.	19.6	16.0	19.2	15.0	17.5	27.5	10.1	3.9	7.1
in.	0.77	0.63	0.76	0.59	0.69	1.08	0.40	0.15	0.28

PERFORMANCE DETAILS

Specifications	
Contact Type:	Crimp
Max. Matings:	5000
Contact Retention:	22 N
Contact Dia.:	0.7 mm (0.028in)
Bucket Dia.:	0.8 mm (0.031in)
Min. Conductor:	0.14 mm ² (AWG 26)
Max. Conductor:	0.34 mm ² (AWG 22)
R (max):	6.1 mOhm

OTHER CHARACTERISTICS

Humidity (max):	<=95% [at 60 deg C /140 F]
Vibration:	15 g [10 Hz - 2000 Hz]
Shock Resistance:	100 g [6 ms]
Operating temperature:	-55°C/ +200°C
Climatical Category:	15/200/21 (Al. shell)
Lighting strike EIA 364-75	10K amps - 6 times
EMI Shielding EIA 364-66A	- 1Ghz-80 dB,3GHz-70 dB,6GHz- 58dB
IP Rating	68
Catalog	

[Copyright](#) [Privacy policy](#) [Product safety](#)