




D

C

B

A





211769-1, -2, -4 & -5

D

C

B

A



211769-3

1. CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
2. WILL ACCEPT NINE (9) MULTIMATE SOCKET CONTACTS.
3. 3.81[.150] MAXIMUM INSULATION DIAMETER.
4. 2.54[.100] MAXIMUM INSULATION DIAMETER.

YES	FLANGE	211769-5
NO	FLANGE	211769-4
NO	FREE HANGING	211769-3
NO	FLANGE	211769-2
NO	FLANGE	211769-1
THREADED INSERTS	MOUNTING	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.BROCKWAY 09-24-94	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK R.STONE 09-30-94	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPV A.FRANTUM 10-03-94	RECEPTACLE HOUSING, REVERSE SEX, SHELL SIZE 17, CPC	
0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC	SIZE A1	
MATERIAL -		FINISH -	CAGE CODE 00779	
WEIGHT -		RESTRICTED TO	DRAWING NO 211769	
CUSTOMER DRAWING		SCALE 2:1	SHEET 1 OF 1	
		REV G1		