




E = .000100" PURE TIN, MATTE OVERALL



PART NUMBER	POSITIONS/ CONTACTS	A		B		C	
		INCH	MM	INCH	MM	INCH	MM
SFH31-NP_B-D03-SP-__	03/06	0.100	2.54	0.167	4.23	0.220	5.58
SFH31-NP_B-D04-SP-__	04/08	0.150	3.81	0.217	5.50	0.270	6.85
SFH31-NP_B-D05-SP-__	05/10	0.200	5.08	0.267	6.77	0.320	8.12
SFH31-NP_B-D06-SP-__	06/12	0.250	6.35	0.317	8.04	0.370	9.39
SFH31-NP_B-D07-SP-__	07/14	0.300	7.62	0.367	9.31	0.420	10.66
SFH31-NP_B-D08-SP-__	08/16	0.350	8.89	0.417	10.58	0.470	11.93
SFH31-NP_B-D09-SP-__	09/18	0.400	10.16	0.467	11.85	0.520	13.20
SFH31-NP_B-D10-SP-__	10/20	0.450	11.43	0.517	13.12	0.570	14.47
SFH31-NP_B-D11-SP-__	11/22	0.500	12.70	0.567	14.39	0.620	15.74
SFH31-NP_B-D12-SP-__	12/24	0.550	13.97	0.617	15.66	0.670	17.01
SFH31-NP_B-D13-SP-__	13/26	0.600	15.24	0.667	16.93	0.720	18.28
SFH31-NP_B-D14-SP-__	14/28	0.650	16.51	0.717	18.20	0.770	19.55
SFH31-NP_B-D15-SP-__	15/30	0.700	17.78	0.767	19.47	0.820	20.82
SFH31-NP_B-D16-SP-__	16/32	0.750	19.05	0.817	20.74	0.870	22.09
SFH31-NP_B-D17-SP-__	17/34	0.800	20.32	0.867	22.01	0.920	23.36
SFH31-NP_B-D18-SP-__	18/36	0.850	21.59	0.917	23.28	0.970	24.63
SFH31-NP_B-D19-SP-__	19/38	0.900	22.86	0.967	24.55	1.020	25.90
SFH31-NP_B-D20-SP-__	20/40	0.950	24.13	1.017	25.82	1.070	27.17
SFH31-NP_B-D21-SP-__	21/42	1.000	25.40	1.067	27.09	1.120	28.44
SFH31-NP_B-D22-SP-__	22/44	1.050	26.67	1.117	28.36	1.170	29.71
SFH31-NP_B-D23-SP-__	23/46	1.100	27.94	1.167	29.63	1.220	30.98
SFH31-NP_B-D24-SP-__	24/48	1.150	29.21	1.217	30.90	1.270	32.25
SFH31-NP_B-D25-SP-__	25/50	1.200	30.48	1.267	32.17	1.320	33.52
SFH31-NP_B-D26-SP-__	26/52	1.250	31.75	1.317	33.44	1.370	34.79
SFH31-NP_B-D27-SP-__	27/54	1.300	33.02	1.367	34.71	1.420	36.06
SFH31-NP_B-D28-SP-__	28/56	1.350	34.29	1.417	35.98	1.470	37.33
SFH31-NP_B-D29-SP-__	29/58	1.400	35.56	1.467	37.25	1.520	38.60
SFH31-NP_B-D30-SP-__	30/60	1.450	36.83	1.517	38.52	1.570	39.87
SFH31-NP_B-D31-SP-__	31/62	1.500	38.10	1.567	39.79	1.620	41.14
SFH31-NP_B-D32-SP-__	32/64	1.550	39.37	1.617	41.06	1.670	42.41
SFH31-NP_B-D33-SP-__	33/66	1.600	40.64	1.667	42.33	1.720	43.68
SFH31-NP_B-D34-SP-__	34/68	1.650	41.91	1.717	43.60	1.770	44.95
SFH31-NP_B-D35-SP-__	35/70	1.700	43.18	1.767	44.87	1.820	46.22
SFH31-NP_B-D36-SP-__	36/72	1.750	44.45	1.817	46.14	1.870	47.49
SFH31-NP_B-D37-SP-__	37/74	1.800	45.72	1.867	47.41	1.920	48.76
SFH31-NP_B-D38-SP-__	38/76	1.850	46.99	1.917	48.68	1.970	50.03
SFH31-NP_B-D39-SP-__	39/78	1.900	48.26	1.967	49.95	2.020	51.30
SFH31-NP_B-D40-SP-__	40/80	1.950	49.53	2.017	51.22	2.070	52.57
SFH31-NP_B-D41-SP-__	41/82	2.000	50.80	2.067	52.49	2.120	53.84
SFH31-NP_B-D42-SP-__	42/84	2.050	52.07	2.117	53.76	2.170	55.11
SFH31-NP_B-D43-SP-__	43/86	2.100	53.34	2.167	55.03	2.220	56.38
SFH31-NP_B-D44-SP-__	44/88	2.150	54.61	2.217	56.30	2.270	57.65
SFH31-NP_B-D45-SP-__	45/90	2.200	55.88	2.267	57.57	2.320	58.9



CUSTOMER COPY

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES [MM] TOLERANCES: ANGULAR: DECIMALS .XX= ± .012 [.3] .XXX= ± .008 [.20] .XXXX= ± .0040 [.100]	DRAWN		DATE	NAME		
			10/31/08	JH		
	THE INFORMATION HEREIN CONTAINS PROPRIETARY INFORMATION OF SULLINS ELECTRONICS AND IS NOT TO BE REPRODUCED, USED OR DISCLOSED TO OTHERS FOR ANY PURPOSE EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY AN OFFICER OF SULLINS ELECTRONICS.			TITLE		
				HEADER FEMALE, .050[1.27] CC, SMT		
				PART NUMBER	SFH31-NP_B-D__-SP-__	
		SIZE	CAGE CODE	DWG. NO.	REV	
		C	54453		C11165	F
	SCALE: 2:1			SHEET 1 OF 1		