



Helawrap Cable Cover

- Helawrap HWPP

Helawrap is used to bundle and protect cables in the electrical industry, panel building, machine, automotive and truck manufacturing. Helawrap in 25m lengths is the time-saving solution for industrial applications.

Helawrap in practical 2m lengths is designed for domestic and office use. It puts an end to the cable chaos associated with PCs, TVs and Hi-Fi systems.

Features and Benefits

- Ideal solution for bundling, protecting, mounting and routing cables
- Quick and effortless to apply
- Good abrasion protection
- Special profile enables branching off cable at any point
- Can be removed and reapplied often
- Available in several colours and sizes
- Handy applicator tool included

MATERIAL	Polypropylene (PP)
Operating Temperature	-60 °C to +110 °C, intermittent +140 °C
Flammability	UL94 HB



Helawrap made of flame-retardant polyamide 6 can be found in the Engineered Solutions Catalogue.



One Step to the Web!



Complete cable management for home and office.



Helawrap, the fast and easy solution to your cable chaos, available in 2 sizes and 3 colours!



Insert one or more cables into the insertion slot of the applicator tool.



Place the applicator tool in one end of the Helawrap cable cover.



Simply slide the applicator tool through the Helawrap cover.



Helawrap Cable Cover

• Helawrap HWPP

TYPE	Bundle Ø max.	Colour	Reel Length	Application Tool	Article-No.
HWPP8	9	Black (BK)	25 m	HAT8	161-64101
	9	Grey (GY)	25 m	HAT8	161-64102
	9	Silver (SR)	25 m	HAT8	161-64103
	9	White (WH)	25 m	HAT8	161-64104
HWPP16	16	Black (BK)	25 m	HAT16	161-64201
	16	Grey (GY)	25 m	HAT16	161-64202
	16	Silver (SR)	25 m	HAT16	161-64203
	16	White (WH)	25 m	HAT16	161-64207
HWPP20	21	Black (BK)	25 m	HAT20	161-64301
	21	Grey (GY)	25 m	HAT20	161-64302
	21	Silver (SR)	25 m	HAT20	161-64303
	21	White (WH)	25 m	HAT20	161-64304
HWPP25	27	Black (BK)	25 m	HAT25	161-64401
	27	Grey (GY)	25 m	HAT25	161-64402
	27	Silver (SR)	25 m	HAT25	161-64403
	27	White (WH)	25 m	HAT25	161-64407
HWPP30	32	Black (BK)	25 m	HAT30	161-64501
	32	Grey (GY)	25 m	HAT30	161-64502
	32	Silver (SR)	25 m	HAT30	161-64503
	32	White (WH)	25 m	HAT30	161-64504

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content.

TYPE	Bundle Ø max.	Colour	Length (L)	Application Tool	Article-No.
HWPP16L2	16	Black (BK)	2 m	HAT16	161-64204
	16	Grey (GY)	2 m	HAT16	161-64205
	16	Silver (SR)	2 m	HAT16	161-64206
HWPP25L2	27	Black (BK)	2 m	HAT25	161-64404
	27	Grey (GY)	2 m	HAT25	161-64405
	27	Silver (SR)	2 m	HAT25	161-64406

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content.