



Designed to Accept Industry's Most Extensive Line of Audio/Video Connectors, UTP, Coax, and Fiber Keystone Connectors.

Rear, Flush Mounting Improves Tamper-Resistance.

FEATURES

- Flush Keystone mounting.
- Single or Double-gang versions available.
- Field configurable.

SPECIFICATIONS

- ◆ Type 430 stainless steel.
- ◆ Brushed stainless steel finish.
- ◆ Rear housing of Noryl®.
- ◆ 3/4" stainless steel mounting screws supplied.
- ◆ Dimensions:
 - SSF1: 2.75"W x 4.5"H.
 - SSF2: 4.5"W x 4.5"H.

STANDARDS/LISTINGS/VERIFICATIONS

APPLICATIONS

- ▲ Medical Facilities.
- ▲ Laboratories.
- ▲ Manufacturing Plants.
- ▲ Education Facilities.

Face Plates, Stainless Steel



Stainless Steel Faceplates - SSF, are designed for flush mount applications, accepting Hubbell's extensive line of **XCELERATOR™** jacks and Audio/Video connectors that snap mount flush into the keystone opening, creating an elegant streamline look.

This attractive plate can be configured for a multitude of environments such as medical facilities, manufacturing plants, and school systems where reliability, durability, and tamper-resistance are critical elements in choosing the appropriate plate.

ORDERING INFORMATION

SSF Stainless Steel Plates



	Single-gang					Double-gang				
	1-port	2-port	3-port	4-port	6-port	4-port	6-port	9-port	12-port	
Unit Package	1 per Bag	1 per Bag	1 per Bag	1 per Bag	1 per Bag	1 per Bag	1 per Bag	1 per Bag	1 per Bag	
Order Qty.	Carton of 25	Carton of 25	Carton of 25	Carton of 25	Carton of 25	Carton of 10	Carton of 10	Carton of 10	Carton of 10	
Catalog No.	SSF11	SSF12	SSF13	SSF14	SSF16	SSF204	SSF206	SSF209	SSF212	

NOTE: All SSF plates will accept Audio/Video keystone connectors and XCELERATOR™ jacks.

SSF Stainless Steel Plate with Label Fields

Order Information

Single-gang	1-port	2-port	3-port	4-port	6-port
Unit Package	1 per Bag	1 per Bag	1 per Bag	1 per Bag	1 per Bag
Order Qty.	Carton of 25	Carton of 25	Carton of 25	Carton of 25	Carton of 25
Catalog No.	SSFL11	SSFL12	SSFL13	SSFL14	SSFL16



SSFL13

NOTE: All SSF plates will accept Audio/Video keystone connectors and XCELERATOR™ jacks.

ACCESSORIES

XCELERATOR™ Jacks, Category 6 and 5e

Catalog No.

Category 5e

HXJ5EXX

Category 6

HXJ6XX

XX = Color:

'AL' = Almond

'B' = Blue

'BK' = Black

'EI' = Electric Ivory

'GL25' = Gold*

'GY' = Gray

'GN' = Green

* 25-packs only.

'OW' = Office White

'OR' = Orange

'P25' = Purple*

'R' = Red

'TI' = Telco Ivory

'W' = White

'Y' = Yellow



Patch Cords, Category 6 and 5e

Catalog No.

Category 5e

PCX5EXX*

Category 6

PCX6XX**

XX = Standard Color:

'B' = Blue; 'BK' = Black;

'GY' = Gray; 'Y' = Yellow

For other colors replace color designation with one of the following:

OR = Orange, R = Red, GN = Green, P = Purple, W = White

* = Standard Length: '01'=1'; '03'=3'; '05'=5'; '07'=7'; '10'=10'; '15'=15'; '20'=20'; '25'=25'; '30'=30'; '35'=35'; '40'=40'; '45'=45'; '50'=50'; '55'=55'; '60'=60'; '75'=75'; '100'=100'

** = Standard Length: '03' = 3'; '06' = 6'; '08' = 8'; '10' = 10'; '12' = 12'; '16' = 16'; '20' = 20'



UTP Cable, SPEEDGAIN® Category 5E, 4-Pair



Color	Catalog No. Riser Spool	REELEX*	Catalog No. Plenum Spool	REELEX*
Blue	C5EPSRB	C5EPRRB	C5EPSPB	C5EPRPB
Gray	C5EPSRGY	C5EPRRGY	C5EPSPGY	C5EPRPGY
White	C5EPSRW	C5EPRRW	C5EPSPW	C5EPRPW
Yellow	C5EPSRY	C5EPRRY	C5EPSPY	C5EPRPY

* REELEX is licensed and patented by Windings Inc.

UTP Cable, NEXTSPEED® Category 6, 4-Pair



Color	Catalog No. Riser Spool	REELEX*	Catalog No. Plenum Spool	REELEX*
Blue	C6SRB	C6RRB	C6SPB	C6RPB
Gray	C6SRGY	C6RRGY	C6SPGY	C6RPGY
White	C6SRW	C6RRW	C6SPW	C6RPW
Yellow	C6SRY	C6RRY	C6SPY	C6RPY

* REELEX is licensed and patented by Windings Inc.



Hubbell Premise Wiring

HUBBELL INCORPORATED (Delaware)

14 Lord's Hill Road • Stonington, CT 06378-0901 • (860) 535-8326 • 800-626-0005

Fax: (860) 535-8328 • Internet site: <http://www.hubbell-premise.com>

Worldwide Locations

Hubbell Premise Wiring, Asia Pacific	852-2836-7131	Fax: 852-2836-7132
Hubbell Canada Inc.	905-839-1138	Fax: 905-839-9108
Hubbell Premise Wiring, Central America	506-309-4158	Fax: 506-260-1616
Hubbell Premise Wiring, China	8621-6309-0119	Fax: 8621-6309-0122
Hubbell Premise Wiring, Colombia	571-245-8940	Fax: 571-340-0925
Hubbell Premise Wiring, Europe	44-01283 500500	Fax: 44-01283 500400
Hubbell Int'l. Inc., Korea Branch	82-2-(0)2607-1363	Fax: 82-2-(0)2603-7386

Hubbell Premise Wiring, Latin America	305-408-4501	Fax: 305-408-8201
Hubbell de Mexico, S.A. de C.V.	(5255) 9151-9999	Fax: (5255) 9151-9989
Hubbell Premise Wiring, Middle East	971-4-393-4192	Fax: 971-4-393-4194
Hubbell-Taian Co., Ltd., Taiwan	886-2-2522-1862	Fax: 886-2-2522-1872
Hubbell Premise Wiring, Turkey	90-216-313-5016	Fax: 90-216-414-8148
Hubbell Premise Wiring, Venezuela	58-416-680-7453	Fax: 58-281-274-7900

DS-C18 08/05