


Ferrules UNINSULATED (INDUSTRIAL STANDARD)

Uninsulated ferrules <Tin-plated electrolytic copper>



DIN 46228, part 1, except #

Model No.	Applicable wire		Style	Dimensions (mm)			
	mm2	AWG		L1	D1	S	D2
WE0.25-6 #	0.25	24	I	5	0.8	0.15	1.7
WE0.5-10	0.50	20	I	10	1.0	0.15	2.1
WE0.75-10	0.75	18	I	10	1.2	0.15	2.3
WE1-10	1.00	18	I	10	1.4	0.15	2.5
WE1.5-10	1.50	16	I	10	1.7	0.15	2.8
WE2.5-10	2.50	14	I	10	2.2	0.15	3.4
WE4-12	4.00	12	I	12	2.8	0.20	4.0
WE6-15	6.00	10	I	15	3.5	0.20	4.7
WE10-15	10.0	8	I	15	4.5	0.20	5.8
WE16-15	16.0	6	I	15	5.8	0.20	7.5
WE25-15	25.0	4	I	15	7.3	0.20	9.5
WE35-18	35.0	2	I	18	8.3	0.20	11
WE50-22 #	50.0	1	I	22	10.3	0.30	13

Note: 1) Style I - Suitable for Tri-rated cable, Style II - Standard
2) Maximum operating temperature: + 105°C
3) Delivery lead times may vary depending on the product. These products are **ONLY** available from the following JST affiliates;
J.S.T. (U.K.) Ltd, J.S.T. Belgium N.V., J.S.T. India Liaison Office, and JST-SouthAfrica.com.