


Tab Contacts

**Tabs 9.5 x 1.2 mm
with Steel Top Spring,
Mates with AMP MCP 9.5
Contact System**

Extraction Tool:
Part No. **1-1579007-7**



Standard Tab Contacts (STC)

Wire Size Range (mm ²)	Insulation Diameter (mm)		Material and Finish *	Part Numbers				Applicator	Hand Tool
	FLK	FLR		Strip Form	Package Quantity	Loose- Piece	Package Quantity		
2.5-4.0	3.3-4.7	-	-1 / -2	963764	700	963765	500	2-878793-2	734532-1
4.0-6.0	4.0-5.2	-	-1 / -2	963766	700	963767	500		
6.0-10.0	4.7-6.6	-	-1 / -2	963768	700	963769	500		

Tab Contacts Single Wire Sealing System (SWS)

Wire Size Range (mm ²)	Insulation Diameter (mm)		Material and Finish *	Part Numbers				Applicator	Hand Tool
	FLK	FLR		Strip Form	Package Quantity	Loose- Piece	Package Quantity		
2.5-4.0	4.0-4.5	-	-1 / -2	963770	550	963771	500	2-878734-2	-
4.0-6.0	4.7-5.3	-	-1 / -2	963772	550	963773	500		
6.0-10.0	6.2-6.6	-	-1 / -2	963774	550	963775	500		

***) Material and Finish:**

- 1 = CuSn, pre-tin plated
- 2 = CuFe, pre-tin plated